



# CERTIFICATE

No. Z2 13 08 18349 008



Product Service

**Model(s):** ALPHA2 25-40 180 Model B

**Parameters:**

Rated voltage:	230 V
Rated frequency:	50 Hz
Rated input :	max. 18 W
Delivery height H:	4 m
Delivery rate Q (at 1 m height):	2,7 m <sup>3</sup> /h
Rated pressure:	max. 10 bar
Max. allowed media temperature:	110° C
Energy-Efficiency-Index EEI:	0,15
Energy-consumption:	44 kWh (5000 op.h)

The mentioned product is on the 1st place in a comparison test from 7 different manufacturers in terms of energy efficiency and energy consumption.

The complete and detailed test result is in the below mentioned testreport.

**Tested according to:** PPP 11093B:2012

**Production Facility(ies):** 18349